



AMD Technologies, Inc.
 218 Bronwood Avenue
 Los Angeles, CA 90049-3104

T 310.471.8900
 T 800.423.3535
 F 310.471.8900

W amdtechnologies.com
 W digitalams.com
 E info@amdtechnologies.com

Apron Sizing and Protection

Step 1: Select your apron style from our catalog.

Step 2: Use your measurements to find the correct width and length from these charts.

FRONT PROTECTION APRONS

Model Names: Economy Tie, EasyWrap, Buckle, FlexBack, BackRelief and Surgery Drop-off

Model Numbers: 201XX, 202XX, 205XX, 206XX, 221XX and 222XX – where “XX” is replaced by the size number

Size	Chest	Height	Apron Width	Apron Length	Size Number “XX”
Small	32”-38”	4’11”-5’5”	20”	32”	05
	81-96 cm	149-165 cm	cm	80 cm	
Average	38”-42”	5’5”-5’8”	22”	34”	15
	96-106 cm	165-172 cm	cm	86 cm	
Large	42”-46”	5’8”-5’11”	24”	36”	25
	106-116 cm	172-180 cm	cm	90 cm	
X-Large-Tall	42”-46”	5’11”-6’2”	24”	38”	35
	106-116 cm	180-188 cm	cm	96 cm	
XX	47”-52”	5’8”-5’11”	27”	36”	45
	119-132 cm	172-180 cm	cm	90 cm	
XXL-Tall	47”-52”	5’11”-6’2”	27”	38”	55
	119-132 cm	180-188 cm	cm	96 cm	

Cetermeter sizes rounded down to nearest whole number.

WRAP AROUND (FRONT AND BACK) PROTECTION APRONS

Model Name: Special Procedure

Model Number: 203XX – where “XX” is replaced by the size number

Size	Chest	Waist	Hips (up to)	Height	Apron Circumference	Apron Length	Size Number “XX”
Small	34”-37”	27”-31	39”	4’11”-5’5”	45”	32”	05
	86-94 cm	68-78 cm	99 cm	149-165 cm	114 cm	80 cm	
Average	38”-41”	31”-35”	43”	5’5”-5’8”	50”	34”	15
	96-104 cm	78-88 cm	109 cm	165-172 cm	127 cm	86 cm	
Large	42”-45”	35”-39”	47”	5’8”-5’11”	54”	36”	25
	106-114 cm	88-99 cm	119 cm	172-180 cm	137 cm	90 cm	
X-Large-Tall	46”-49”	39”-43”	51”	5’11”-6’2”	54”	38”	35
	116-124 cm	99-109 cm	129 cm	180-188 cm	137 cm	96 cm	
XX	50”-53”	43”-47”	55”	5’8”-5’11”	56”	36”	45
	127-134 cm	109-119 cm	139 cm	172-180 cm	142 cm	90 cm	
XXL-Tall	50”-53”	43”-47”	55”	5’11”-6’2”	56”	38”	55
	127-134 cm	109-119 cm	139 cm	180-188 cm	142 cm	96 cm	

Cetermeter sizes rounded down to nearest whole number.

VEST/SKIRT (FRONT AND BACK) PROTECTION APRONS

Model Name: Vest and Skirt Special Procedure

Model Number: 204XX – where “XX” is replaced by the size number

Size	Chest	Vest Length	Waist	Hips (up to)	Skirt Length	Size Number “XX”
Small	34”-37”	18”	27”-31	39”	21”	05
	86-94 cm	45 cm	68-78 cm	99 cm	53 cm	
Average	38”-41”	19”	31”-35”	43”	22”	15
	96-104 cm	48 cm	78-88 cm	109 cm	55 cm	
Large	42”-45”	20”	35”-39”	47”	22”	25
	106-114 cm	50 cm	88-99 cm	119 cm	55 cm	
X-Large-Tall	46”-49”	22”	39”-43”	51”	23”	35
	116-124 cm	55 cm	99-109 cm	129 cm	58 cm	
XX	50”-53”	21”	43”-47”	55”	22”	45
	127-134 cm	53 cm	109-119 cm	139 cm	55 cm	
XXL-Tall	50”-53”	22”	43”-47”	55”	23”	55
	127-134 cm	55 cm	109-119 cm	139 cm	58 cm	

Cetermeter sizes rounded down to nearest whole number.




AMD Technologies, Inc.
 218 Bronwood Avenue
 Los Angeles, CA 90049-3104

T 310.471.8900
 T 800.423.3535
 F 310.471.8900

W amdtechnologies.com
 W digitalams.com
 E info@amdtechnologies.com

Apron Sizing and Protection

Step 3: ...or customize your sizing by using this chart



All Frontal and Wrap Around Protection

(C) CHEST: Measure widest part 1" below armhole.
 (W) WAIST: Measure narrowest part 1" above navel.
 (H) HIPS: Measure widest part of hips.
 LENGTH: We recommend 1" above the knee.

NOTE YOUR RESULTS HERE:

CHEST: _____
 WAIST: _____
 HIPS: _____
 LENGTH: _____
 LENGTH VEST: _____ SKIRT: _____
 PROTECTION (CIRCLE) RL TL NL



Two piece Vest/Skirt

Step 4: Choice your protection from this chart.

Protection Options (Frontal Aprons) Add proper initials for optional protection when ordering. Otherwise Regular Lead is standard.	RL-Regular Lead*	TL-TL lite Ply*	NL-Non Lead**
	Standard – 0.5 mm Pb Eq	Standard – 0.5 mm Pb Eq	Standard – 0.5 mm Pb Eq
	RLL	TLL	NLL
	Optional – 0.35 mm Pb eq	Optional – 0.35 mm Pb eq	Optional – 0.235 mm Pb eq

Protection Options (Wrap Around Aprons) Add proper initials for optional protection when ordering. Otherwise Regular Lead is standard.	RL-Regular Lead*			Lightweight Choice		
	Standard			TL – TL Light Ply* or NL – Non Lead **		
	Front	Front	Front	Front	Front	Front
	0.5 mm Pb eq	0.3 mm Pb eq	1.0 mm Pb eq	0.5 mm Pb eq	0.3 mm Pb eq	1.0 mm Pb eq
RLL – Regular Lead*			TLL – TL Lite Ply*			
Front	Front	Front	Front	Front	Front	
0.35 mm Pb eq	0.25 mm Pb eq	0.7 mm Pb eq	0.35 mm Pb eq	0.25 mm Pb eq	0.7 mm Pb eq	

Protection Options (Wrap Around Aprons) Add proper initials for optional protection when ordering. Otherwise Regular Lead is standard.	RL-Regular Lead*			Lightweight Choice			
	Standard			TL – TL Light Ply* or NL – Non Lead **			
	Vest:	Front	Back	Overlap	Front	Back	Overlap
	Skirt:	0.5 mm Pb eq	0.3mm Pb eq	1.0mm Pb eq	0.5mm Pb eq	0.25mm Pb eq	1.0mm Pb eq
		0.3mm Pb Eq	0.3mm Pb Eq	0.6mm Pb Eq	0.25mm Pb Eq	0.25mm Pb Eq	0.6mm Pb Eq
RLL – Regular Lead*			TLL – TL Lite Ply*				
Vest:	Front	Back	Overlap	Front	Back	Overlap	
Skirt:	0.35mm Pb eq	0.25mm Pb eq	0.7mm Pb eq	0.35mm Pb eq	0.25mm Pb eq	0.7mm Pb eq	
	0.25mm Pb Eq	0.25mm Pb Eq	0.5mm Pb Eq	0.25mm Pb Eq	0.25mm Pb Eq	0.5mm Pb Eq	

* Denotes lead equivalency of Regular Lead or RLL and TL Lite Ply or TLL @ 100 kVp.

** Denotes lead equivalency of NL Non Lead or NLL @ 90 kVp.

Note: For proper protection in your working environment please contact a radiation physicist regarding adequate apron Pb equivalency.

Refer to custom options or contact us regarding prices on alternate protection options. Discounts may apply when reducing Pb equivalency.